J.D. Nicoud, Mouette 5 CH-1092 Belmont, Switzerland Tel +41 21 728-6156, Fax 728-6157 Email info@didel.com, www.didel.com



Micro gears

Gears at module 0.3 are available from **"DIDEL**; they are well suited for motors 3 to 10 mm in diameter. Four gear sizes are available, and for the two large sizes, slotted gears allows to add photodiodes and get precise angle and speed information.


Module and teeth number

The module is the quotient of the nominal diameter of a gear by the number of teeth. For instance, a module 0.3 gear of 60 teeth has a nominal diameter of 0.3 x 60 = 18 mm. Add two teeth for the external diameter, which will be measured as 18.6 mm. The distance between the axis of two gears is simply the module multiplied by the total number of teeth, divided by 2. Add 0.05 to 0.1 mm to be sure the movement will be free. Distance has to be precise for long lasting gears and for reaching the efficiency of 90% one can expect for every stage.

Plastic gears of module 0.3

Gears have a center hole of 0.76 to 0.79 mm. They press—fit on a 0.8mm axis (ream out at 0.78mm) and are loose on a 0.75mm axis. In this case, it is recommended to ream out the hole with a 0.82 reamer and use a 0.8 mm steel axis.

id# num	Teeth lber		Weigh g	tDia nom	Dia ext	Dia hole	Stock #	Price \$	(1 pied CHF	te)
#1	12		0.04	3 .6	4.2	0.78	500			
#2	36/12		0.13	10.8	11.4	0.78	300			
#3	36/12	side	0.17	10.8	11.4	0.78	100			
	48/12	light		14.4	15.0	0.78	not	availab	le	
#5	48/12	36 slots	0.19	14.4	15.0	0.78	200			
#4b	60/12	light	0.18	18.0	18.6	0.78	250			
#4	60/12	60 Slots	0.25	18.0	18.6	0.78	200			



Distance between axis

12	to 3	36	7.2	mm	plus	0.07	mm	play
12	to 4	48	9.0	mm	plus	0.07	mm	play
12	to 6	50	10.8	mm	plus	0.07	mm	play

Pager motors (preliminary offer)

#id	Make	Weight g	Coil Ohm	V/mA	Dia mot	Length mot	Dia axis	Total length	l piece CHF)
	XT-5966 XR5165PE SM5360F	0.56 1.04 1.73		1.3/90 1.3/90 1.3/	6 .05 6 .05 8	10 15	0.8 0.8 0.8	15 15 20 15		
	switec	7 .6		5/10	30	10	8.0	20		

RIC324 JDN-DIDEL 23:54:33 09/11/00 8890 @TYPO:#MM0:@TYPO:#MM0:MICROGEARS.TF 1

Mouse encoder for **DIDEL** microgears

DIDEL encoder uses the H7101 proprietary circuit and provides two signals in quadrature, in response to a light pattern formed of alternating 0.31mm dark and lighted stripes. There are indeed four diodes and two differential amplifiers inside. The histeresis provided by these amplifiers allows not to respect this precise pattern. A large dark or bright slot shoud not trigger any change in the output. With a standard IR LED, a strong lighting is required for full speed, but the LED can be pulsed. A 30 μ s pulse set the inside triggers according to the light pattern and informations stays on the outputs until next light pulse. Sampling frequency depends on the rotation speed.





Fig 1. Principle of the photodiodes

The circuit is packaged in a 4-pin black transistor-like case (fig 2). The circuit is bonded on the flat area side. The infrared LED available in the same package are bonded on the side of the lens.

Interfacing the circuit does not need any additional component. Power supply is +5V, 0.1mA, and the output are CMOS compatible, and can dirrectly be fed to a microcontroller input port.

Encoder and microgears

The **DIDEL** 48 and 60 teeth gears include respectively 36 and 60 slots compatible with the H7101 encoder. Relative dimensions are documented below (fig3).






Fig 3. Encoder position relative to microgears November, 9th 1900 **DIDEL**